

Description	HiTemp140-TSK		HiTemp140-F	PT-TSK	
Temperature Sensor		100	Ω platinum RTD		
Temperature Range	−200 °C to +260 °C (-328 °F to	+500 °F)	-200 °C to +350 °C (-32	28 °F to +662 °F)	
Temperature Resolution		0.01 °C			
remperature resolution			n)		
Temperature Accuracy	±0.1 °C/±0.18 °F (20 °C to +140 °C/68 °F to +284 °F) ±0.3 °C/±0.54 °F (-20 °C to +19.99 °C/4 °F to +67.98 °F) ±0.4 °C/±0.72 °F (-40 °C to -20.01 °C/-40 °F to -4.02 °F)				
Memory	32,700 readings				
Reading Rate	1 reading every second up to 1 reading every 24 hours				
Required Interface Package	IFC400 or IFC406 USB docking station required; 125,000 baud				
Typical Battery Life	1 year (1 minute reading rate at 25 °C/77 °F)				
Operating Environment	-40 °C to +140 °C (-40 °F to +284 °F), 0 %RH to 100 %RH				
Material	· · ·				
	Data Logger: 316 stainless steel, Thermal Shield: PTFE				
Dimensions: Body	2.7 in x 0.97 in dia. (67 mm x 25 mm dia.)				
Dimensions: Shield	Flush Top: 2.75 in \times 2.0 in dia. (69.85 mm \times 51 mm dia.) Vented Top: 4.3 in \times 2.0 in dia. (109.2 mm \times 51 mm dia.)				
Dimensions: HiTemp140-5.25-TSK		5.25 in x 0.188 in dia. (134 mm x 4.8 mm dia.)		n/a	
Dimensions: HiTemp140-7-TSK	7.0 in x 0.188 in dia. (178 mm x 4.8 mm dia		n/a	n/a	
Dimensions: HiTemp140-PT-1-TSK	n/a	Prob		be tip: 1.7 in x 0.125 in dia. (42 mm x 3.2 mm dia.) le portion: 22 in x 0.062 in dia. (559 mm x 1.6 mm dia.)	
Dimensions: HiTemp140-PT-5-TSK	n/a (121 mi		21 mm x 3.2 mm dia. with 25 r	p: 4.8 in x 0.125 in dia. with 1 in x 0.188 in dia. handle nm x 3.2 mm dia. with 25 mm x 4.8 mm dia. handle) portion: 22 in x 0.062 in dia. (559 mm x 1.6 mm dia.)	
	Flush Top: 8.2 oz (232.5 g) (not including data logger) Vented Top: 9.9 oz (280.7 g) (not including data logger)				
Weight		n Top: 8.2 oz (23	2.5 g) (not including data logg	er)	
		n Top: 8.2 oz (23	2.5 g) (not including data logg	er)	
Approvals	Vente	n Top: 8.2 oz (23 ed Top: 9.9 oz (2	2.5 g) (not including data logg 80.7 g) (not including data logg CE	er) ger)	
		n Top: 8.2 oz (23 ed Top: 9.9 oz (2	2.5 g) (not including data logg 80.7 g) (not including data logg CE	er)	
Approvals Maximum Exposure	Vente	n Top: 8.2 oz (23 ed Top: 9.9 oz (2	2.5 g) (not including data logg 80.7 g) (not including data logg CE HiTemp14	er) ger)	
Approvals Maximum Exposure Time Chart	Vente	n Top: 8.2 oz (23 ed Top: 9.9 oz (29 6 (Flush)	2.5 g) (not including data logg 80.7 g) (not including data logg CE HiTemp14	er) ger) 10-TS (Vented)	
Approvals Maximum Exposure Time Chart Ambient Tempertature	Vente HiTemp 140-TS Exposure Time in Air Exp	n Top: 8.2 oz (23 ed Top: 9.9 oz (2) o (Flush)	2.5 g) (not including data logg 80.7 g) (not including data logg CE HiTemp14	er) ger) 10-TS (Vented) Exposure Time In Liquid	
Approvals Maximum Exposure Time Chart Ambient Tempertature -200 °C (-328 °F)	HiTemp140-TS Exposure Time in Air Exp 12 minutes	n Top: 8.2 oz (23 d Top: 9.9 oz (23 6 (Flush) posure Time In L N/A	2.5 g) (not including data logg 30.7 g) (not including data logg CE HiTemp14 quid Exposure Time in Air 14 minutes	er) ger) 10-TS (Vented) Exposure Time In Liquid N/A	
Approvals Maximum Exposure Time Chart Ambient Tempertature -200 °C (-328 °F) -180 °C (-292 °F)	HiTemp140-TS Exposure Time in Air Exp 12 minutes 13 minutes	Top: 8.2 oz (23 d Top: 9.9 oz (26 f Top: 9.9 oz	2.5 g) (not including data logg 80.7 g) (not including data logg CE HITemp14 quid Exposure Time in Air 14 minutes	er) gger) 10-TS (Vented) Exposure Time In Liquid N/A N/A	
Approvals Maximum Exposure Time Chart Ambient Tempertature -200 °C (-328 °F) -160 °C (-292 °F) -160 °C (-256 °F)	HiTemp140-TS Exposure Time in Air 12 minutes 13 minutes 15 minutes	n Top: 8.2 oz (23 d Top: 9.9 oz (23 6 (Flush) cosure Time In L N/A N/A N/A	2.5 g) (not including data logg 80.7 g) (not including data logs CE HITemp14 quid Exposure Time in Air 14 minutes 15 minutes 16 minutes	er) ger) 10-TS (Vented) Exposure Time In Liquid N/A N/A N/A	
Approvals Maximum Exposure Time Chart Ambient Tempertature -200 °C (-328 °F) -180 °C (-292 °F) -160 °C (-256 °F) -140 °C (-220 °F)	HiTemp 140-TS Exposure Time in Air Exp 12 minutes 13 minutes 15 minutes 17 minutes	n Top: 8.2 oz (23 d Top: 9.9 oz (2i 5 (Flush) Dosure Time In L N/A N/A N/A	2.5 g) (not including data logg 80.7 g) (not including data logg CE HITemp14 quid Exposure Time in Air 14 minutes 15 minutes 16 minutes	er) ger) 10-TS (Vented) Exposure Time In Liquid N/A N/A N/A N/A N/A	
Approvals Maximum Exposure Time Chart Ambient Tempertature -200 °C (-328 °F) -180 °C (-292 °F) -160 °C (-220 °F) -140 °C (-220 °F) -120 °C (-184 °F)	HiTemp 140-TS Exposure Time in Air Exp 12 minutes 13 minutes 15 minutes 17 minutes 19 minutes	n Top: 8.2 oz (23 dd Top: 9.9 oz (25 dd Top: 9.9 oz	2.5 g) (not including data logg 90.7 g) (not including data logs CE HITemp14 quid Exposure Time in Air 14 minutes 15 minutes 18 minutes 21 minutes	er) ger) O-TS (Vented) Exposure Time In Liquid N/A N/A N/A N/A N/A N/A	
Approvals Maximum Exposure Time Chart Ambient Tempertature -200 °C (-328 °F) -180 °C (-292 °F) -160 °C (-256 °F) -140 °C (-220 °F) -120 °C (-184 °F) -100 °C (-148 °F) -80 °C (-112 °F)	HiTemp 140-TS Exposure Time in Air Exp 12 minutes 13 minutes 15 minutes 17 minutes 19 minutes 22 minutes	n Top: 8.2 oz (23 dd Top: 9.9 oz (25 dd Top: 9.9 oz	2.5 g) (not including data logg 80.7 g) (not including data logs CE HITemp14 quid Exposure Time in Air 14 minutes 15 minutes 16 minutes 18 minutes 21 minutes 21 minutes	er) ger) IO-TS (Vented) Exposure Time In Liquid N/A N/A N/A N/A N/A N/A N/A N/A N/A	
Approvals Maximum Exposure Time Chart Ambient Tempertature -200 °C (-328 °F) -180 °C (-292 °F) -160 °C (-220 °F) -140 °C (-220 °F) -120 °C (-184 °F) -100 °C (-148 °F)	HiTemp 140-TS Exposure Time in Air 12 minutes 13 minutes 15 minutes 17 minutes 19 minutes 22 minutes 27 minutes	n Top: 8.2 oz (23 did Top: 9.9 oz (26 did Top:	2.5 g) (not including data logg 80.7 g) (not including data logg CE HITemp14 quid Exposure Time in Air 14 minutes 15 minutes 16 minutes 21 minutes 21 minutes 24 minutes 30 minutes	er) ger) IO-TS (Vented) Exposure Time In Liquid N/A N/A N/A N/A N/A N/A N/A N/	
Approvals Maximum Exposure Time Chart Ambient Temperature -200 °C (-328 °F) -180 °C (-222 °F) -160 °C (-256 °F) -140 °C (-220 °F) -120 °C (-184 °F) -100 °C (-184 °F) -80 °C (-172 °F) -40 °C (-76 °F) -40 °C (-40 °F to +284 °F)	HiTemp 140-TS Exposure Time in Air 12 minutes 13 minutes 15 minutes 17 minutes 19 minutes 22 minutes 27 minutes 37 minutes	n Top: 8.2 oz (23 did Top: 9.9 oz (25 did Top:	2.5 g) (not including data logg 80.7 g) (not including data logg CE HITemp14 quid Exposure Time in Air 14 minutes 15 minutes 18 minutes 21 minutes 24 minutes 30 minutes	er) ger) IO-TS (Vented) Exposure Time In Liquid N/A N/A N/A N/A N/A N/A N/A N/	
Approvals Maximum Exposure Time Chart Ambient Tempertature -200 °C (-328 °F) -180 °C (-292 °F) -160 °C (-220 °F) -140 °C (-220 °F) -120 °C (-148 °F) -100 °C (-148 °F) -80 °C (-112 °F) -40 °C (-76 °F) -40 °C (-76 °F) -40 °C (-40 °F to +284 °F) -150 °C (302 °F)	HiTemp 140-TS Exposure Time in Air 12 minutes 13 minutes 15 minutes 17 minutes 19 minutes 22 minutes 27 minutes 37 minutes Indefinitely	n Top: 8.2 oz (23 d Top: 9.9 oz (23 d Top: 9.9 oz (24 d Top: 9.9 o	2.5 g) (not including data logg 30.7 g) (not including data logs CE HITemp14 quid Exposure Time in Air 14 minutes 15 minutes 16 minutes 21 minutes 24 minutes 30 minutes 42 minutes 42 minutes 18 minutes 18 minutes 19 minutes 19 minutes 10 minutes 10 minutes 11 minutes 12 minutes 13 minutes 14 minutes 15 minutes 17 minutes 18 minutes 18 minutes 19 minutes 19 minutes 10 minutes 10 minutes 10 minutes 10 minutes 10 minutes 11 minutes 12 minutes 13 minutes 14 minutes 15 minutes 16 minutes 17 minutes 18 minutes 18 minutes 18 minutes 19 minutes 19 minutes 10 min	er) per) Exposure Time In Liquid N/A	
Approvals Maximum Exposure Time Chart Ambient Tempertature -200 °C (-328 °F) -180 °C (-292 °F) -160 °C (-220 °F) -140 °C (-220 °F) -120 °C (-148 °F) -100 °C (-112 °F) -80 °C (-112 °F) -40 °C (-6 °F) -40 °C to +140 °C (-40 °F to +284 °F) 150 °C (320 °F) 160 °C (320 °F)	HITemp 140-TS Exposure Time in Air 12 minutes 13 minutes 15 minutes 17 minutes 19 minutes 22 minutes 27 minutes 37 minutes 19 minutes 51 minutes 51 minutes	n Top: 8.2 oz (23 d Top: 9.9 oz (2) d Top: 9.9 oz (2) 5 (Flush) sosure Time In L N/A N/A N/A N/A N/A N/A N/A N/	2.5 g) (not including data logg 80.7 g) (not including data logs CE HITemp14 quid Exposure Time in Air 14 minutes 15 minutes 16 minutes 21 minutes 21 minutes 30 minutes 42 minutes 42 minutes 42 minutes 46 minutes 66 minutes	er) ger) IO-TS (Vented) Exposure Time In Liquid N/A N/A N/A N/A N/A N/A N/A N/	
Approvals Maximum Exposure Time Chart Ambient Tempertature -200 °C (-32.8 °F) -180 °C (-22.5 °F) -160 °C (-25.6 °F) -140 °C (-22.0 °F) -120 °C (-184 °F) -100 °C (-184 °F) -80 °C (-112 °F) -40 °C (-16 °F) -40 °C (-32.0 °F) -40 °C (-30.2 °F) -150 °C (30.2 °F) -160 °C (32.0 °F) -170 °C (33.0 °F) -170 °C (33.0 °F) -170 °C (33.0 °F)	HITemp 140-TS Exposure Time in Air Exp 12 minutes 13 minutes 15 minutes 17 minutes 19 minutes 22 minutes 27 minutes 18 minutes 19 minutes 29 minutes 20 minutes 20 minutes 21 minutes 22 minutes 37 minutes 38 minutes 39 minutes	n Top: 8.2 oz (23 d Top: 9.9 oz (21 d Top: 9.9 o	2.5 g) (not including data logg 90.7 g) (not including data logs CE HITemp14 Leading Exposure Time in Air 14 minutes 15 minutes 18 minutes 18 minutes 21 minutes 24 minutes 42 minutes 42 minutes 42 minutes 46 minutes 66 minutes 18 minutes 47 minutes 48 minutes 49 minutes 49 minutes 49 minutes 40 minutes 40 minutes 10	er) ger) DO-TS (Vented) Exposure Time In Liquid N/A	
Approvals Maximum Exposure Time Chart Ambient Tempertature -200 °C (-328 °F) -180 °C (-292 °F) -160 °C (-226 °F) -140 °C (-220 °F) -120 °C (-148 °F) -100 °C (-148 °F) -80 °C (-112 °F) -40 °C (-76 °F) -40 °C to +140 °C (-40 °F to +284 °F) 150 °C (302 °F) 160 °C (320 °F) 170 °C (338 °F) 180 °C (356 °F)	HITemp 140-TS Exposure Time in Air	n Top: 8.2 oz (23 d Top: 9.9 oz (2: d Top: 9.9 o	2.5 g) (not including data logg 90.7 g) (not including data logs 90.7 g) (not including data logs CE HITemp14 Exposure Time in Air 14 minutes 15 minutes 16 minutes 18 minutes 21 minutes 24 minutes 42 minutes 47 minutes 18 minutes 48 minutes 48 minutes 48 minutes 48 minutes 48 minutes 49 minutes	Exposure Time In Liquid N/A	
Approvals Maximum Exposure Time Chart Ambient Temperature -200 °C (-238 °F) -180 °C (-292 °F) -160 °C (-292 °F) -140 °C (-220 °F) -120 °C (-148 °F) -100 °C (-148 °F) -80 °C (-112 °F) -60 °C (-76 °F) -40 °C to +140 °C (-40 °F to +284 °F) 150 °C (320 °F) 170 °C (338 °F) 180 °C (336 °F) 180 °C (336 °F) 180 °C (374 °F)	HITemp 140-TS Exposure Time in Air 12 minutes 13 minutes 15 minutes 17 minutes 19 minutes 22 minutes 27 minutes 37 minutes 19 minutes 43 minutes 43 minutes 34 minutes	n Top: 8.2 oz (23 d Top: 9.9 oz (2) d Top: 9.9 oz (2) 5 (Flush) 5 (Flush) N/A N/A N/A N/A N/A N/A N/A N/	2.5 g) (not including data logg 80.7 g) (not including data logs CE HITemp14 quid Exposure Time in Air 14 minutes 15 minutes 18 minutes 21 minutes 24 minutes 30 minutes 42 minutes 42 minutes 48 minutes 48 minutes 48 minutes	er) ger) IO-TS (Vented) Exposure Time In Liquid N/A N/A N/A N/A N/A N/A N/A N/	
Approvals Maximum Exposure Time Chart Ambient Tempertature -200 °C (-328 °F) -180 °C (-228 °F) -160 °C (-256 °F) -140 °C (-256 °F) -120 °C (-184 °F) -100 °C (-184 °F) -80 °C (-112 °F) -40 °C (-184 °F) -40 °C (-76 °F) -40 °C (-302 °F) -150 °C (302 °F) -150 °C (338 °F) -170 °C (338 °F) -180 °C (336 °F) -190 °C (336 °F) -190 °C (337 °F) -190 °C (337 °F) -190 °C (337 °F)	HITemp 140-TS Exposure Time in Air Exp 12 minutes 13 minutes 15 minutes 15 minutes 19 minutes 22 minutes 27 minutes 37 minutes Indefinitely 59 minutes 51 minutes 43 minutes 43 minutes 37 minutes 43 minutes 33 minutes 43 minutes 34 minutes 31 minutes	n Top: 8.2 oz (23 d Top: 9.9 oz (21 d Top: 9.9 o	2.5 g) (not including data logg 30.7 g) (not including data logs 30.7 g) (not including data logs CE HITemp14 quid Exposure Time in Air 14 minutes 15 minutes 16 minutes 21 minutes 24 minutes 30 minutes 42 minutes 42 minutes 42 minutes 42 minutes 42 minutes 57 minutes 48 minutes 42 minutes 42 minutes 38 minutes 38 minutes 38 minutes 38 minutes 34 minutes	er) ger) Exposure Time In Liquid N/A	
Approvals Maximum Exposure Time Chart Ambient Tempertature -200 °C (-328 °F) -180 °C (-292 °F) -160 °C (-225 °F) -140 °C (-220 °F) -120 °C (-184 °F) -100 °C (-148 °F) -80 °C (-112 °F) -60 °C (-76 °F) -40 °C to +140 °C (-40 °F to +284 °F) 150 °C (302 °F) 160 °C (320 °F) 170 °C (338 °F) 180 °C (356 °F) 190 °C (374 °F) -200 °C (374 °F) -200 °C (372 °F) -210 °C (410 °F)	HITemp 140-TS Exposure Time in Air	n Top: 8.2 oz (23 d Top: 9.9 oz (2) d Top: 9.9 oz (2) 5 (Flush) oosure Time In L. N/A	2.5 g) (not including data logg 90.7 g) (not including data logs 90.7 g) (not including data logs CE HITemp14 Exposure Time in Air 14 minutes 15 minutes 16 minutes 21 minutes 24 minutes 42 minutes 42 minutes 42 minutes 42 minutes 42 minutes 42 minutes 30 minutes 42 minutes 42 minutes 43 minutes 43 minutes 43 minutes 43 minutes 43 minutes 42 minutes 38 minutes 38 minutes 34 minutes 34 minutes 32 minutes 32 minutes 32 minutes 32 minutes 32 minutes	er) ger) Exposure Time In Liquid N/A	
Approvals Maximum Exposure Time Chart Ambient Tempertature -200 °C (-328 °F) -180 °C (-222 °F) -160 °C (-226 °F) -140 °C (-220 °F) -100 °C (-148 °F) -100 °C (-148 °F) -80 °C (-112 °F) -60 °C (-76 °F) -40 °C to +140 °C (-40 °F to +248 °F) 150 °C (320 °F) 170 °C (338 °F) 180 °C (356 °F) 190 °C (374 °F) 200 °C (374 °F) 200 °C (372 °F) 210 °C (410 °F) 220 °C (428 °F)	HITemp 140-TS Exposure Time in Air 12 minutes 13 minutes 15 minutes 17 minutes 19 minutes 22 minutes 27 minutes Indefinitely 59 minutes 43 minutes 43 minutes 34 minutes 34 minutes 31 minutes 29 minutes 27 minutes	n Top: 8.2 oz (23 d Top: 9.9 oz (2) d Top: 9.9 oz (2) d Top: 9.9 oz (2) f (Flush) ossure Time In L N/A	2.5 g) (not including data logg 90.7 g) (not including data logg CE HITemp14 quid Exposure Time in Air 14 minutes 15 minutes 18 minutes 21 minutes 24 minutes 42 minutes 42 minutes 48 minutes 48 minutes 48 minutes 48 minutes 48 minutes 48 minutes 49 minutes 40 minutes 41 minutes 42 minutes 43 minutes 44 minutes 45 minutes 46 minutes 47 minutes 48 minutes 49 minutes 40 minutes 41 minutes 42 minutes 43 minutes 44 minutes 45 minutes 46 minutes 47 minutes 48 minutes 49 minutes 40 minutes 40 minutes 41 minutes 42 minutes 43 minutes 44 minutes 45 minutes 46 minutes 47 minutes 48 minutes 49 minutes 40 minutes 40 minutes 41 minutes 42 minutes 43 minutes	er) ger) Exposure Time In Liquid N/A N/A N/A N/A N/A N/A N/A N/A A N/A A N/A A N/A S S minutes Indefinitely 40 minutes 29 minutes 26 minutes 26 minutes 21 minutes 11 minutes 13 minutes 13 minutes	
Approvals Maximum Exposure Time Chart Ambient Tempertature -200 °C (-328 °F) -180 °C (-225 °F) -160 °C (-256 °F) -140 °C (-220 °F) -120 °C (-184 °F) -100 °C (-184 °F) -80 °C (-112 °F) -60 °C (-76 °F) -40 °C (-140 °C (-200 °F) -40 °C (-300 °F) -150 °C (300 °F) -150 °C (330 °F) -160 °C (330 °F) -170 °C (338 °F) -180 °C (336 °F) -190 °C (336 °F) -190 °C (336 °F) -190 °C (392 °F) -210 °C (410 °F) -220 °C (428 °F) -230 °C (448 °F) -230 °C (448 °F)	HITemp 140-TS Exposure Time in Air 12 minutes 13 minutes 15 minutes 15 minutes 19 minutes 22 minutes 27 minutes 19 minutes 37 minutes 11 minutes 11 minutes 12 minutes 12 minutes 13 minutes 14 minutes 15 minutes 16 minutes 17 minutes 18 minutes 19 minutes 19 minutes 10 minu	n Top: 8.2 oz (23 d Top: 9.9 oz (21 d Top: 9.9 o	2.5 g) (not including data logg 30.7 g) (not including data logs 30.7 g) (not including data logs CE HITemp14 quid Exposure Time in Air 14 minutes 15 minutes 16 minutes 21 minutes 24 minutes 30 minutes 42 minutes 42 minutes 42 minutes 42 minutes 42 minutes 33 minutes 42 minutes 43 minutes 43 minutes 43 minutes 43 minutes 34 minutes 32 minutes 30 minutes 30 minutes	er) per) Exposure Time In Liquid N/A	
Approvals Maximum Exposure Time Chart Ambient Temperature -200 °C (-328 °F) -180 °C (-292 °F) -160 °C (-220 °F) -140 °C (-220 °F) -100 °C (-148 °F) -100 °C (-148 °F) -80 °C (-112 °F) -60 °C (-76 °F) -40 °C to +140 °C (-40 °F to +284 °F) 150 °C (320 °F) 170 °C (338 °F) 180 °C (356 °F) 190 °C (374 °F) -200 °C (374 °F) -200 °C (374 °F) -210 °C (410 °F) -220 °C (428 °F)	HITemp 140-TS Exposure Time in Air 12 minutes 13 minutes 15 minutes 17 minutes 19 minutes 22 minutes 27 minutes Indefinitely 59 minutes 43 minutes 43 minutes 34 minutes 34 minutes 31 minutes 29 minutes 27 minutes	n Top: 8.2 oz (23 d Top: 9.9 oz (2) d Top: 9.9 oz (2) d Top: 9.9 oz (2) f (Flush) ossure Time In L N/A	2.5 g) (not including data logg 90.7 g) (not including data logg CE HITemp14 quid Exposure Time in Air 14 minutes 15 minutes 18 minutes 21 minutes 24 minutes 42 minutes 42 minutes 48 minutes 48 minutes 48 minutes 48 minutes 48 minutes 48 minutes 49 minutes 40 minutes 41 minutes 42 minutes 43 minutes 44 minutes 45 minutes 46 minutes 47 minutes 48 minutes 49 minutes 40 minutes 41 minutes 42 minutes 43 minutes 44 minutes 45 minutes 46 minutes 47 minutes 48 minutes 49 minutes 40 minutes 40 minutes 41 minutes 42 minutes 43 minutes 44 minutes 45 minutes 46 minutes 47 minutes 48 minutes 49 minutes 40 minutes 40 minutes 41 minutes 42 minutes 43 minutes	er) ger) Exposure Time In Liquid N/A N/A N/A N/A N/A N/A N/A N/A A N/A S S indefinitely 40 minutes 34 minutes 29 minutes 26 minutes 23 minutes 21 minutes 19 minutes 18 minutes	

Product User Guide



HiTemp140-PT-TSK

High Temperature Data Logger with a 24 inch Stainless Steel Flexible Probe and Thermal Shield

HiTemp140-TSK

High Temperature Data Logger with Thermal Shield



To view the full MadgeTech product line, visit our website

REV 12 2019.01.25

HiTemp140-TSK and HiTemp140-PT-TSK

Product Notes

Getting Started

The HiTemp140-TSK consists of a HiTemp140 data logger in a thermal enclosure and the HiTemp140-PT-TSK consists of a HiTemp140-PT data logger in a thermal enclosure. They can be used in both wet and dry applications up to 140 °C indefinitely. When used with the thermal enclosure the devices can withstand higher temperatures for certain durations of time. The chart located on the back page, outlines the time versus temperature durations.

- To start the logger, unscrew the thermal enclosure and separate the thermal enclosure lid, from the body of the data logger.
- The logger should be removed from the barrier immediately after removal from the heat environment. Be extremely careful, the logger may be very hot.

Submergibility

The HiTemp140 and the HiTemp140-PT are fully submergible and are rated IP68. They can be placed in environments with up to 230 feet (70 m) of water.

Installation Guide

Installing the Interface cable

- IFC400 or IFC406

Refer to the "Quick Start Guide" included in the package.

Installing the software

Insert the Software USB stick in an open USB port. If the autorun does not appear, locate the drive on the computer and double click on **Autorun.exe**. Follow the instructions provided in the Wizard.

Device Operation

Connecting and Starting the data logger

- $\hbox{-} Once the software is installed and running, plug the interface cable into the docking station.\\$
- Connect the USB end of the interface cable into an open USB port on the computer.
- The device will appear in the Connected Devices list, highlight the desired data logger.
- For most applications, select "Custom Start" from the menu bar and choose the desired start method, reading rate and other parameters appropriate for the data logging application and click "Start". ("Quick Start" applies the most recent custom start options, "Batch Start" is used for managing multiple loggers at once, "Real Time Start" stores the dataset as it records while connected to the logger.)
- The status of the device will change to "Running", "Waiting to Start" or "Waiting to Manual Start", depending upon your start method.
- Disconnect the data logger from the interface cable and place it in the environment to measure.

Note: The device will stop recording data when the end of memory is reached or the device is stopped. At this point the device cannot be restarted until it has been re-armed by the computer.

Downloading data from a data logger

- Place the logger into the docking station.
- Highlight the data logger in the ${\bf Connected\ Devices}$ list. Click "Stop" on the menu bar.
- Once the data logger is stopped, with the logger highlighted, click "Download". You will be prompted to name your report.
- Downloading will offload and save all the recorded data to the PC.

Device Maintenance

Battery Replacement

Materials:

ER1425S-HT Battery

- Unscrew the bottom of the logger and remove the battery.
- Place the new battery into the logger. Note the polarity of the battery.
- Screw the cover back onto the logger.

Recalibration

The HiTemp140 and HiTemp140-PT standard calibrations are two points at 30 °C and 140 °C.

Prices and specifications subject to change. See MadgeTech's terms and conditions

Disclaimer and Terms of Use

Listed specifications can be used to determine maximum allowable exposure times for the HiTemp140 with Thermal Shield at different temperatures beyond the normal operating range of the logger. Both the data logger and Thermal Shield must be at ambient temperature (approximately 25 °C) before being placed in the extreme temperature environment. Immediately following exposure to high temperature, the data logger should be removed from the thermal shield (using appropriate precautions, as it could be VERY hot) OR the data logger and shield should be placed in a water bath (approximately 25 °C) for at least 15 minutes to allow it to cool. Failing to do this may allow heat trapped in the Thermal Shield to continue to heat the data logger to potentially unsafe levels.

If your application involves a ramp up to a temperature above 140 °C and/or any complex temperature profile that isn't simply a constant temperature, please contact MadgeTech to determine whether the HiTemp140 with Thermal Shield is suitable.

Please provide MadgeTech with a detailed description of your temperature profile, including temperatures, durations, ramp times, and process media (air, steam, oil, water, etc.)

Battery Warning

WARNING: FIRE, EXPLOSION, AND SEVERE BURN HAZARD. DO NOT SHORT CIRCUIT, CHARGE, FORCE OVER DISCHARGE, DISASSEMBLE, CRUSH, PENETRATE OR INCINERATE. BATTERY MAY LEAK OR EXPLODE IF HEATED ABOVE 140 °C (288 °F).

Specifications subject to change.
See MadgeTech's terms and conditions